


ILLUMINATOR DATA-ID

CAS2-00-100-X-B-24V



Mechanical Information	
Cooling Material	Alamatatan
Casing Material	Aluminium
Storage Temperature Range	Temp 0 - 45°C, Humidity 20-85%
Weight	1310 g
Length / Outer Diameter	166.5 mm
Width / Inner Diameter	120 mm
Thickness / Height	123.8 mm



CAS2-00-100-X-B-24V

Optical Information						
Part Number	CAS2-00-100-X-B-24V					
LED Color			BLUE			
Wavelength	(nm)	470				
Intensity (±15%)	(Lux)	10700	9100	7800		
Working Distance	(mm)	40	50	60		
Illumination (number of row)			X			
Illumination Active Area	, ,					
Active Length / Outer Diameter	(mm)	100				
Active Width / Inner Diameter	(mm)		100			
Emission angle Eye Safety Class (IEC62471)	(deg.)	0 II				
Lye Safety Class (TEC02471)			"			
Electrical Information						
Lighting Supply Voltage						
(constant voltage mode)		24V ± 2%				
Continuous Current	(mA)	781				
Power Consumption	(W)		18.74			
Lighting casing temperature,						
Operating after 60 minutes	°C	48.6				
Strobe Mode Specification						
Pulse Operation		YES				
Max. Lighting Supply Voltage	4.4					
(Constant voltage power supply)	(V)	Pulsing at 24VDC to 48VDC, 0-10% Duty Cycle, Recommended at 36VDC				
Pulse Current, (Max. 10msec)	(1)	2042				
(Constant current power supply)	(mA)	2343				
Max. Trigger Pulse Duration	(msec)	10				
Duty Cycle	0-10%					
Additional Information						
Additional Cooling Method		Attached to machine part for better heat dissipation				
Intensity Controller Selection		ANG, ST, SD and SDA Series				
CE Conformity		YES				
RoHS Compliance	YES					
Connection						
Connector Type (Default):		ICT CMD O2V				
Connector Type (Default): Cable Length out from lighting:	(mm)	JST SMR-03V 500				
Pin Configuration :	(111111)	Pin	Signal	Cable Color		
The Configuration .		1	LED +	RED		
		2	N.C.			
		3	LED -	WHITE		
				·····-		
Application						
Illumination Type		Coaxial Illumination				
Applicattion Use		Surface inspection and alignment, wafer, metal surface, film, LCD and glass, pattern on PCB.				



Thank you for downloading this document from www.machine-vision-shop.com

If you have any questions, you need help composing the right package for your application or do you want to order?

Feel free to contact us via e-mail at sales@vision-consultancy.nl or visit our webshop.

Our vision experts are happy to help you.



Natascha Overhof



Christian Crompvoets



VISION CONSULTANCY

Robert Schumandomein 2 6229 ES Maastricht The Netherlands

+31 (0) 438 522 651

sales@vision-consultancy.nl www.machine-vision-shop.com

