


Lighting Dimension



ROHS CE

Mechanical Information	
Casing Material	Aluminium
Storage Temperature Range	Temp 0-45°C, Humidity 20-85%
Weight	145 g
Length / Outer Diameter	81 mm
Width / Inner Diameter	36.2 mm
Thickness / Height	35 mm

ILLUMINATOR DATA-ID

DLR3-60-080-1-B-24V


TMS

Optical Information						
Part Number		[DLR3-60-080-1-B-24V			
LED Color			BLUE			
Wavelength	(nm)		525			
Intensity (±15%)	(Lux)	TBA		TBA		
Working Distance	(mm)	5		13		
Illumination (number of row)			1			
Illumination Active Area						
Active Length / Outer Diameter	(mm)	69				
Active Width / Inner Diameter	(mm)	38.2				
Emission angle	(deg.)	60				
Eye Safety Class (IEC62471)		ll				
Electrical Information						
Lighting Supply Voltage		1				
(constant voltage mode)		24V ± 2%				
Continuous Current	(mA)	180				
Power Consumption	(W)	4.32				
Lighting casing temperature, Operating after 60 minutes		1	F1			
Operating after 60 minutes	Ľ	°C 51				
Strobe Mode Specification						
Pulse Operation		YES				
Max. Lighting Supply Voltage	0.0	Pulsing at 24VDC to 48VDC, 0-10% Duty Cycle				
(Constant voltage power supply)	(∨)	Recommended at 36VDC				
Pulse Current, (Max. 10msec)	<i>(</i>)					
(Constant current power supply)	(mA)	540				
Max. Trigger Pulse Duration	(msec)	(msec) 10				
Duty Cycle		0-10%				
Additional Information						
Additional Cooling Method		Attached to machine part for better heat dissipation				
Intensity Controller Selection		ANG, ST, SD and SDA Series				
CE Conformity		YES				
RoHS Compliance		YES				
Connection						
Connector Type (Default):		JST SMR-03V				
Cable Length out from lighting :	(mm)	500				
Pin Configuration :	()	Pin	Signal	Cable Color		
an comparation .		1	LED +	RED		
		2	N.C.			
		3	LED -	WHITE		
			-			
		<u> </u>				
Application						
		Diffured Illumination				
Illumination Type		Diffused Illumination				
Applicattion Use		Character recognition on shining surface, lead inspection				



ILLUMINATOR DATA-ID

DLR3-60-080-1-B-24V





Thank you for downloading this document from www.machine-vision-shop.com

If you have any questions, you need help composing the right package for your application or do you want to order?

Feel free to contact us via e-mail at sales@visionconsultancy.nl or visit our webshop.

Our vision experts are happy to help you.



Natascha Overhof



Christian Crompvoets



VISION CONSULTANCY

Robert Schumandomein 2 6229 ES Maastricht The Netherlands

+31 (0) 438 522 651

sales@vision-consultancy.nl www.machine-vision-shop.com Scan me to visit machine-vision-shop

